

**Garant**
**Boring bar steel, right-hand, Shank Ø / insert size: 0810/06mm**


## Order data

Order number	260032 0810/06
GTIN	4045197979001
Item class	21T

## Technical description

Insert size	6 mm
Overall length L	110 mm
ISO code toolholder	A0810J SCLCR/L06
Pack of insert screws	269028 7
Setting angle $\kappa$	95 degrees
Head length $L_1$	27 mm
Minimum pre-drill $\varnothing D_{\min}$	11 mm
suitable indexable insert	CC.. 0602..
Clamping height $L_2$	9 mm
Neck width $L_4$	8 mm
Centre offset $L_3$	6 mm
Shank $\varnothing D_s$	10 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar

---

**Accessories**

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8

674248 TX8

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500