

Garant
Boring bar steel, right-hand, Shank Ø / insert size: 0608/06mm


Order data

Order number	260032 0608/06
GTIN	4045197978790
Item class	21T

Technical description

Setting angle κ	95 degrees
suitable indexable insert	CC.. 0602..
Neck width L_4	6 mm
Clamping height L_2	7 mm
Insert size	6 mm
Pack of insert screws	269028 7
Minimum pre-drill $\varnothing D_{\min}$	8 mm
Head length L_1	21.5 mm
Centre offset L_3	4.2 mm
Overall length L	100 mm
ISO code toolholder	A0608H SCLCR/L06
Shank $\varnothing D_s$	8 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8

674248 TX8

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500