

Garant
Boring bar steel, left-hand, Shank \varnothing / insert size: 1216/06mm


Order data

Order number	260033 1216/06
GTIN	4045197979063
Item class	21T

Technical description

Head length L_1	42 mm
Pack of insert screws	269028 7
Minimum pre-drill $\varnothing D_{\min}$	16 mm
Neck width L_4	12 mm
suitable indexable insert	CC.. 0602..
ISO code toolholder	A1216M SCLCR/L06
Insert size	6 mm
Setting angle κ	95 degrees
Centre offset L_3	8.9 mm
Clamping height L_2	15 mm
Overall length L	150 mm
Shank $\varnothing D_s$	16 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8

674248 TX8

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500