

Garant
Boring bar steel, left-hand, Shank \varnothing / insert size: 0810/06mm


Order data

Order number	260033 0810/06
GTIN	4045197979049
Item class	21T

Technical description

Centre offset L_3	6 mm
suitable indexable insert	CC.. 0602..
Minimum pre-drill $\varnothing D_{\min}$	11 mm
Clamping height L_2	9 mm
Pack of insert screws	269028 7
Insert size	6 mm
ISO code toolholder	A0810J SCLCR/L06
Head length L_1	27 mm
Neck width L_4	8 mm
Setting angle κ	95 degrees
Overall length L	110 mm
Shank $\varnothing D_s$	10 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8

674248 TX8

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500