

Garant
Boring bar steel, left-hand, Shank \varnothing / insert size: 1012/06mm


Order data

Order number	260033 1012/06
GTIN	4045197979056
Item class	21T

Technical description

Minimum pre-drill $\varnothing D_{\min}$	13 mm
suitable indexable insert	CC.. 0602..
Overall length L	125 mm
Centre offset L_3	6.9 mm
Pack of insert screws	269028 7
Head length L_1	32.5 mm
Insert size	6 mm
Setting angle κ	95 degrees
Clamping height L_2	11 mm
Neck width L_4	10 mm
ISO code toolholder	A1012K SCLCR/L06
Shank $\varnothing D_s$	12 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8

674248 TX8

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500