

**Garant**
**Boring bar steel, right-hand, Shank Ø / insert size: 0810/07mm**

**Order data**

Order number	260342 0810/07
GTIN	4045197979070
Item class	21T

**Technical description**

Overall length L	100 mm
Clamping height L <sub>2</sub>	9 mm
Head length L <sub>1</sub>	22.5 mm
Insert size	7 mm
Minimum pre-drill Ø D <sub>min</sub>	12.5 mm
Pack of insert screws	269028 7
Neck width L <sub>4</sub>	7 mm
Setting angle κ	93 degrees
suitable indexable insert	DC.. 0702..
ISO code toolholder	A0810H SDUCR/L07
Centre offset L <sub>3</sub>	6.5 mm
Usable depth T	4.4 mm
Shank Ø D <sub>s</sub>	10 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar

---

## Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500