

Garant
Boring bar steel, left-hand, Shank \varnothing / insert size: 1216/07mm

Order data

Order number	260343 1216/07
GTIN	4045197979124
Item class	21T

Technical description

Clamping height L_2	15 mm
suitable indexable insert	DC.. 0702..
Minimum pre-drill $\varnothing D_{\min}$	18 mm
Setting angle κ	93 degrees
Neck width L_4	12 mm
ISO code toolholder	A1216M SDUCR/L07
Head length L_1	40.5 mm
Overall length L	150 mm
Insert size	7 mm
Centre offset L_3	11 mm
Pack of insert screws	269028 7
Usable depth T	4.9 mm
Shank $\varnothing D_s$	16 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500