

**Mitutoyo****Mini-processor / printer DP-1 VA, Type: DP1VA****Order data**

Order number	498701 DP1VA
GTIN	4946368728476
Item class	44A

**Description****Version:**

Fast and quiet data printer. Large easily legible characters. Timed reading of measured values (clock function). Data logging up to 9999 values. Thermal printer paper with long-term stability. Very compact. Press key to start. Powered by 6V mains adapter, batteries or rechargeable batteries. Data logger function with time stamp. Printing and data transmission can be performed concurrently. Compatible with measuring devices with the Digimatic 2 format.

**Printable data:** Measured values; OK / not OK values, number of data, min / max value, range; average value, standard deviation, number of rejects, percentage of rejects, process capability index, histogram, intervention limits; date and time.

**Application:**

For data collection, printing, and statistical evaluation of the measured data of small measuring tools with Digimatic interface.

**Supplied with:**

Supplied with 1 roll thermal paper, carrying strap, and mains adapter.

**Optional extras:**

Thermal paper No. 498710, foot switch No. 498780. Batteries (4 pieces) No. 081570 size LR6, batteries (4 pieces) No. 081561 size. LR6.

## Technical description

Power supply	Rechargeable battery-powered
Interface	Digimatic interface
Interface	RS232C interface
Type of product	Data printer

---

## Accessories

Thermal register paper set, 5 pieces, for No. 498700 Type VR	498710 VR
Set of NiMH rechargeable batteries International size LR6	081570 LR6
Alkaline-manganese batteries International size LR6	081561 LR6
Foot switch for data transmission units	498780