

**Waste bin / ashtray combination, Volume: 40l**

Order data

Order number	987175 40
GTIN	4031068156718
Item class	96S

Description**Version:**

Waste bin of galvanised sheet metal, powder-coated, resistant to UV and the weather. Opening on all four sides to receive waste. Head element / ashtray of perforated stainless steel for stubbing out and disposing of cigarettes.

Separately removable ashtray. Galvanised inner container can be removed when the lockable swing door at the front is opened. Door is locked by a square key lock.

4 plastic feet – the front two are adjustable to accommodated variations in the height of the ground.

Standard:

Nicht brennbar nach DIN 4102, Brandschutzklasse A1.

Supplied with:

Supplied with ashtray, galvanised inner container, attachment template for drilling anchor holes in the ground.

Colour:

Body anthracite RAL 7016 **powder-coated**, header element of brushed stainless steel.

Technical description

Height	815 mm
Depth	350 mm
Capacity	40 l
Width	350 mm
Weight	25.4 kg
Filling volume of ashtray	5 l
Type of product	Ashtray