



## EVOCam II video inspection system with LED angled optics, Type: ECO2503



### Order data

Order number	491896 ECO2503
GTIN	2050001956842
Item class	49B

### Description

#### Version:

Digital full-HD microscope with brilliant live video image quality for precise magnification of objects. Various optional wide-field and precision lenses allow up to 300× magnification with constant image sharpness.

- **Brilliant full-HD video images (1080p / 60 fps).**
- **Large 30 : 1 optical zoom range with many magnification options (up to 300×) and 12× digital zoom.**
- **Effortless image storage either on external media (USB stick) or optional software solution (Vifox). Integrated USB3 interface.**
- **High-quality optics with modern digital technology.**
- **Fast, professional imaging for reliable results.**
- **Integrated 8-point LED ring lamp.**
- **High-quality stand versions for precision and stability.**
- **24 inch full-HD monitor with HDMI input.**

Table stand.

#### Application:

Video inspection system for goods receiving, production and development. Large detailed live image for continuous use and viewing by several users at the same time.

#### Supplied with:

With full HD colour monitor 24 inch, USB stick.

**Optional extras:**

EVO Cam II control panel No. 491898, LED transillumination, WiFi transmitter dongle and additional lenses (0.45 × / 1.00 ×). Movable table 100 × 100.

## Technical description

Stand	Table stand
Magnification (x-times) for perpendicular view	28 - 151
Magnification (x-times) for oblique view	19 - 105
Working distance for perpendicular view	56.5 mm
Resolution individual image maximum	1920×1080 px
Resolution live image maximum	1920×1080 px
Weight	23.5 kg
Working distance for oblique view	35.5 mm
Power supply	Mains operated
Type of product	Video inspection system

## Accessories

EVOcam II control panel Type ECX155	491898 ECX155
-------------------------------------	---------------