



EVOCam II video inspection system with LED angled optics, Type: ECO2504



Order data

Order number	491896 ECO2504
GTIN	2050001956859
Item class	49B

Description

Version:

Digital full-HD microscope with brilliant live video image quality for precise magnification of objects. Various optional wide-field and precision lenses allow up to 300x magnification with constant image sharpness.

- **Brilliant full-HD video images (1080p / 60 fps).**
- **Large 30 : 1 optical zoom range with many magnification options (up to 300x) and 12x digital zoom.**
- **Effortless image storage either on external media (USB stick) or optional software solution (Vifox). Integrated USB3 interface.**
- **High-quality optics with modern digital technology.**
- **Fast, professional imaging for reliable results.**
- **Integrated 8-point LED ring lamp.**
- **High-quality stand versions for precision and stability.**
- **24 inch full-HD monitor with HDMI input.**

Multi-axis column stands (without base plate), focus module.

Application:

Video inspection system for goods receiving, production and development. Large detailed live image for continuous use and viewing by several users at the same time.

Supplied with:

With full HD colour monitor 24 inch, USB stick.

Optional extras:

EVO Cam II control panel No. 491898, LED transillumination, WiFi transmitter dongle and additional lenses (0.45 x / 1.00 x). Base plate No. 491889.

Technical description

Stand	Column stand
Magnification (x-times) for perpendicular view	28 - 151
Weight	35.5 kg
Working distance for oblique view	35.5 mm
Resolution live image maximum	1920×1080 px
Resolution individual image maximum	1920×1080 px
Magnification (x-times) for oblique view	19 - 105
Working distance for perpendicular view	56.5 mm
Power supply	Mains operated
Type of product	Video inspection system

Accessories

EVOCam II control panel Type ECX155	491898 ECX155
Base plate for column stand	491889