

Honeywell**Pair of gloves Polytril™, Glove size: 9****Order data**

Order number	094370 9
GTIN	3603835500058
Item class	09A

Description**Version:**

Polytril™. Gloves with nitrile coating for handling of small parts in greasy, damp and dirty environments.

Standard:

EN 388; EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Manufacturer's designation	Polytril
DMF-free	no
Oil grip	very good
Touch sensitivity	good
Wet grip	good
Material of coating	Nitrile

Breathability	good
Heat protection	not available
Accuracy of fit	very good
Glove size	9
Series	Polytril™
Type of glove	Multi-purpose gloves
Protection category	Category II
Clothing standard	Oeko-Tex Standard 100
Contents	10
Glove characteristics	DMF-free
Glove characteristics	Suitable for allergy sufferers
EN 388	4121X
Backing material	Polyamide
Coating	Nitrile
Coating variant	The palms of the hands
Application range	All-round
Length	220 - 260 mm
Colour	white / grey
Weight	36-50 g
Knitted technology	13G
Application	reusable
Cut protection class	1
Type of product	Multi-purpose gloves