



## Internal extractor set in KUKKO L-BOXX®, Type: 25A



### Order data

Order number	882500 25A
GTIN	4021176013058
Item class	83U

### Description

#### Version:

Consisting of internal bearing extractor and centre reaction piece. **Internal bearing extractor** with 2-piece jaws and spreader.

**Centre reaction piece** of high-quality tool steel, with sturdy spindle, tightening nut, and clamping handle. Internal thrust bearing for easy operation of the support brace nut (Size 1 without thrust bearing). The sets are supplied in a KUKKO L-BOXX® size 136.

#### Application:

For trouble-free extraction of ball bearings etc. Even close flush-fitted ball bearings are gripped securely and pulled out quickly. (The spindle of the support brace is screwed on to the wedge spindle of the internal bearing extractor for extraction.)

#### Content:

1 each internal extractor No. 882600: Size 1-6  
 1 each support brace No. 882800: Size 1 and 2  
 for bores: 12 - 46 mm  
 Weight including box: 6.4 kg

### Technical description

Weight including box	6.4 kg
----------------------	--------

for bores	12 - 46 mm
Type of product	Two-leg extractor

---

## Accessories

Internal extractor single Type 1	882600 1
Internal extractor single Type 4	882600 4
Internal extractor single Type 2	882600 2
Counter support, single Type 2	882800 2
Internal extractor single Type 5	882600 5
Internal extractor single Type 3	882600 3
Internal extractor single Type 6	882600 6
Counter support, single Type 1	882800 1