



Ball bearing installation set in a plastic case



Order data

Order number	884000
GTIN	2050001004338
Item class	86H

Description

Version:

Light but very robust aluminium impact sleeves in combination with 33 extremely impact resistant striking rings for bearing external \varnothing from 26 - 110 mm and internal \varnothing from 10 - 50 mm. Dead-blow hammer with nylon inserts. Supplied in a plastic case.

Application:

Quick, precise, and safe installation of (roller) bearings thanks to **even application of force** on the bearing. Also suitable for fitting of bushes, sealing rings, and pulleys.

Content:

- 3 impact sleeves, \varnothing 25; 40; 60 mm.
- 1 set striking rings internal \varnothing 10 mm (external \varnothing 26; 30; 35 mm)
- 1 set striking rings internal \varnothing 12 mm (external \varnothing 28; 32; 37 mm)
- 1 set striking rings internal \varnothing 15 mm (external \varnothing 32; 35; 42 mm)
- 1 set striking rings internal \varnothing 17 mm (external \varnothing 35; 40; 47 mm)
- 1 set striking rings internal \varnothing 20 mm (external \varnothing 42; 47; 52 mm)
- 1 set striking rings internal \varnothing 25 mm (external \varnothing 47; 52; 62 mm)
- 1 set striking rings internal \varnothing 30 mm (external \varnothing 55; 62; 72 mm)
- 1 set striking rings internal \varnothing 35 mm (external \varnothing 62; 72; 80 mm)
- 1 set striking rings internal \varnothing 40 mm (external \varnothing 68; 80; 90 mm)
- 1 set striking rings internal \varnothing 45 mm (external \varnothing 75; 85; 100 mm)

1 set striking rings internal Ø 50 mm (external Ø 80; 90; 110 mm).

Technical description

Type of product	Impact sleeve
-----------------	---------------

Accessories

A10/26	884005 A10/26
A10/30	884005 A10/30
A10/35	884005 A10/35
A12/28	884005 A12/28
A12/32	884005 A12/32
A12/37	884005 A12/37
A15/32	884005 A15/32
A15/35	884005 A15/35
A15/42	884005 A15/42
A17/35	884005 A17/35
A17/40	884005 A17/40
A17/47	884005 A17/47
B20/42	884005 B20/42
B20/47	884005 B20/47
B20/52	884005 B20/52
B25/47	884005 B25/47
B25/52	884005 B25/52
B25/62	884005 B25/62
B30/55	884005 B30/55
B30/62	884005 B30/62
B30/72	884005 B30/72
C35/62	884005 C35/62

C35/72	884005 C35/72
C35/80	884005 C35/80
C40/68	884005 C40/68
C40/80	884005 C40/80
C40/90	884005 C40/90
C45/75	884005 C45/75
C45/85	884005 C45/85
C45/100	884005 C45/100
C50/80	884005 C50/80
C50/90	884005 C50/90
C50/110	884005 C50/110