



## Internal extractor set in KUKKO L-BOXX®, Type: 25C



### Order data

Order number	882500 25C
GTIN	4021176013218
Item class	83U

### Description

#### Version:

Consisting of internal bearing extractor and centre reaction piece. **Internal bearing extractor** with 2-piece jaws and spreader.

**Centre reaction piece** of high-quality tool steel, with sturdy spindle, tightening nut, and clamping handle. Internal thrust bearing for easy operation of the support brace nut (Size 1 without thrust bearing). The sets are supplied in a KUKKO L-BOXX® size 136.

#### Application:

For trouble-free extraction of ball bearings etc. Even close flush-fitted ball bearings are gripped securely and pulled out quickly. (The spindle of the support brace is screwed on to the wedge spindle of the internal bearing extractor for extraction.)

#### Content:

1 each internal extractor No. 882600: Size 1–7 and 10  
1 each support brace No. 882800: Size 1; 2 and 4

### Technical description

Weight including box	15.2 kg
for bores	12 - 110 mm

Type of product	Two-leg extractor
-----------------	-------------------

## Accessories

Internal extractor single Type 10	882600 10
Internal extractor single Type 7	882600 7
Internal extractor single Type 1	882600 1
Counter support, single Type 4	882800 4
Internal extractor single Type 5	882600 5
Internal extractor single Type 3	882600 3
Internal extractor single Type 6	882600 6
Counter support, single Type 2	882800 2
Counter support, single Type 1	882800 1
Internal extractor single Type 2	882600 2
Internal extractor single Type 4	882600 4