



Internal extractor set in KUKKO L-BOXX®, Type: 25C



Order data

Order number	882500 25C
GTIN	4021176013218
Item class	83U

Description

Version:

Consisting of internal bearing extractor and centre reaction piece. **Internal bearing extractor** with 2-piece jaws and spreader.

Centre reaction piece of high-quality tool steel, with sturdy spindle, tightening nut, and clamping handle. Internal thrust bearing for easy operation of the support brace nut (Size 1 without thrust bearing). The sets are supplied in a KUKKO L-BOXX® size 136.

Application:

For trouble-free extraction of ball bearings etc. Even close flush-fitted ball bearings are gripped securely and pulled out quickly. (The spindle of the support brace is screwed on to the wedge spindle of the internal bearing extractor for extraction.)

Content:

1 each internal extractor No. 882600: Size 1–7 and 10

1 each support brace No. 882800: Size 1; 2 and 4

for bores: 12 - 110 mm

Weight including box: 15.2 kg

Technical description

Weight including box	15.2 kg
----------------------	---------

for bores	12 - 110 mm
Type of product	Two-leg extractor

Accessories

Internal extractor single Type 10	882600 10
Internal extractor single Type 7	882600 7
Internal extractor single Type 1	882600 1
Counter support, single Type 4	882800 4
Internal extractor single Type 5	882600 5
Internal extractor single Type 3	882600 3
Internal extractor single Type 6	882600 6
Counter support, single Type 2	882800 2
Counter support, single Type 1	882800 1
Internal extractor single Type 2	882600 2
Internal extractor single Type 4	882600 4