

**Pair of gloves 03410, Glove size: 8****Order data**

Order number	094423 8
GTIN	4260144424988
Item class	09H

Description**Version:**

Robust gloves of jersey cotton with nitrile coating for medium and heavy applications. Significantly longer life than heavy leather gloves, and more robust and flexible than PVC gloves. Effective barrier against greases and oils. Particularly suitable for rough castings, moulded plastic parts, steel bar, sheet metal, high-tensile cable, building materials, unfinished wood. 03410. With knitted cuffs and 3/4 coating for maintaining better breathability.

Standard:

EN 388; EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Accuracy of fit	good
DMF-free	yes
Material of coating	Nitrile
Glove size	8

Touch sensitivity	medium
Heat protection	not available
silicone-free	yes
Wet grip	very good
Oil grip	medium
Breathability	medium
Protection category	Category II
Type of glove	Multi-purpose gloves
Contents	12
EN 388	4221X
Backing material	Cotton
Coating	Nitrile
Coating variant	3/4 coating
Application range	Heavy Duty
Colour	blue / natural
Weight	40.8 g
Application	reusable
Type of product	Multi-purpose gloves