

**Ansell**
**Pair of gloves HyFlex® 11-920, Glove size: 7**

**Order data**

Order number	094385 7
GTIN	10076490489417
Item class	04P

**Description**
**Version:**

HyFlex® 11-920. With Ansell Grip Technology™: Microscopically small channels in the nitrile coating draw the oil away from the contact surface and ensure a secure grip. Particularly suitable for metal production, general workshop and machine maintenance.

**Standard:**

EN 388; EN ISO 21420

Antistatisch gemäß EN 1149.

**Note:**

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

**Technical description**

Oil grip	very good
Heat protection	not available
Accuracy of fit	very good
Breathability	good
silicone-free	no

DMF-free	no
Material of coating	Nitrile
Wet grip	good
Glove size	7
Touch sensitivity	good
Series	HyFlex®
Protection category	Category II
Type of glove	Multi-purpose gloves
Contents	12
Glove characteristics	Silicone-free
Glove characteristics	free of latex
EN 388	3131A
Backing material	Nylon
Coating	Nitrile
Coating variant	The palms of the hands
Application range	All-round
Length	246 mm
Colour	blue
Weight	25 g
Knitted technology	15G
Application	reusable
Material	Nitrile
Type of product	Multi-purpose gloves