



Spare chisel edge bit, for nuts: M14-M24



Order data

Order number	884910 M14-M24
GTIN	4021176253386
Item class	83U

Description

Version:

With hydraulic ram for splitting jammed or seized nuts (grade 5 – 10) without damaging the bolts. Double curved, allowing operation even where access is difficult. With hardened chisel edge blade. Actuated by tightening the pressure screw. After the nut has been split, unscrew the nut pressure screw and push the chisel back to the stop. Size M18 – M30 for stainless steel nuts - up to M30 in strength class 8, up to M24 in strength class 10.

Suitable for:

No. 884900.

Note:

The pressure screw may be tightened to a **maximum of 60 Nm** for sizes M4 – M14 to a **maximum of 70 Nm** for sizes M14 – M24 and to a **maximum of 120 Nm** for sizes M18 – M30. Do not exceed the tightening torques; excessive torque can break the tool and cause accidents.

Technical description

Chisel edge width	30 mm
for nuts	M14-M24
Type of product	Chisel edge

