

## Storage shelf, add-on rack, Depth 500 mm, Height / Shelf width: 2000/1300mm



### Order data

Order number	990506 2000/1300
GTIN	4004514217691
Item class	96P

### Description

#### Version:

T-profile frames and storage shelves galvanised. Available with a maximum **bay load capacity** of 150 kg per shelf. Storage shelf levels adjustable at 25 mm intervals. Quick assembly thanks to the simple plug-in design.

**Load per bay:** for height 2000 mm 1300 kg, for 2500 mm 1700 kg, for 3000 mm 2300 kg.

#### Description:

#### Assembled size:

**Basic rack:** Nominal length + 60 mm

**Add-on rack:** Nominal length + +6 mm

**Overall depth of the rack:** Nominal depth + 36 mm

#### Application:

Ideal for industry, craft, trade, administration, archives etc. with optimum use of space.

#### Supplied with:

Basic rack with cross braces. One diagonal brace per extension rack.

#### Note:

- **Clamp feet are supplied.**
- **Floor and wall fastenings are not included.**
- **Suitable floor anchoring No. 990854.**
- **Access from one side only due to use of diagonal braces.**

- **The free unsupported length (K) must not be more than 600 mm.**
- **Supplied for self-assembly, saving freight costs. Delivered unassembled.**

## Technical description

Rack height	2000 mm
Number of shelves	5
Rack installation	Extension rack
Number of profile frames	1
Assembled size add-on rack width	1306 mm
Storage shelf depth	500 mm
Rack depth	500 mm
Shelf width	1300 mm
maximum bay load	1300 kg
Shelf load capacity / maximum distributed shelf load (on metal)	150 kg
Shelf thickness	25 mm
Height adjustment interval	25 mm
Type of installation	Plug-in racking
Material	galvanized
Product name attribute	Depth 500 mm
Type of product	Storage shelf

## Accessories

Shelf, galvanised width×depth 1300X500 mm	990580 1300X500
Plug-in dividers, fixed, galvanized Height × depth 400X500 mm	990581 400X500
Plug-in dividers, fixed, galvanized Height × depth 500X500 mm	990581 500X500
	990581 300X500

Plug-in dividers, fixed, galvanized Height x depth 300X500  
mm

Plug-in dividers, fixed, galvanized Height x depth 200X500  
mm

990581 200X500

Clamping base

990852