

Storage shelf, basic rack, Depth 500 mm, Height / Shelf width: 2500/1300mm**Order data**

Order number	990504 2500/1300
GTIN	4004514217592
Item class	96P

Description**Version:**

T-profile frames and storage shelves galvanised. Available with a maximum **bay load capacity** of 150 kg per shelf. Storage shelf levels adjustable at 25 mm intervals. Quick assembly thanks to the simple plug-in design.

Load per bay: for height 2000 mm 1300 kg, for 2500 mm 1700 kg, for 3000 mm 2300 kg.

Description:**Assembled size:**

Basic rack: Nominal length + 60 mm

Add-on rack: Nominal length + +6 mm

Overall depth of the rack: Nominal depth + 36 mm

Application:

Ideal for industry, craft, trade, administration, archives etc. with optimum use of space.

Supplied with:

Basic rack with cross braces. One diagonal brace per extension rack.

Note:

- **Clamp feet are supplied.**
- **Floor and wall fastenings are not included.**
- **Suitable floor anchoring No. 990854.**
- **Access from one side only due to use of diagonal braces.**
- **The free unsupported length (K) must not be more than 600 mm.**

- **Supplied for self-assembly, saving freight costs. Delivered unassembled.**

Technical description

Number of shelves	6
Number of profile frames	2
Assembled size basic rack width	1360 mm
Rack installation	Basic rack
Rack height	2500 mm
Storage shelf depth	500 mm
Rack depth	500 mm
Shelf width	1300 mm
maximum bay load	1800 kg
Shelf load capacity / maximum distributed shelf load (on metal)	150 kg
Shelf thickness	25 mm
Height adjustment interval	25 mm
Type of installation	Plug-in racking
Material	galvanized
Product name attribute	Depth 500 mm
Type of product	Storage shelf

Accessories

Plug-in dividers, fixed, galvanized Height × depth 200X500 mm	990581 200X500
Plug-in dividers, fixed, galvanized Height × depth 500X500 mm	990581 500X500
Shelf, galvanised width×depth 1300X500 mm	990580 1300X500
Plug-in dividers, fixed, galvanized Height × depth 400X500 mm	990581 400X500

Plug-in dividers, fixed, galvanized Height x depth 300X500
mm

990581 300X500

Clamping base

990852