

**Storage shelf, add-on rack, Depth 500 mm, Height / Shelf width:
3000/1300mm****Order data**

Order number	990506 3000/1300
GTIN	4004514217790
Item class	96P

Description**Version:**

T-profile frames and storage shelves galvanised. Available with a maximum **bay load capacity** of 150 kg per shelf. Storage shelf levels adjustable at 25 mm intervals. Quick assembly thanks to the simple plug-in design.

Load per bay: for height 2000 mm 1300 kg, for 2500 mm 1700 kg, for 3000 mm 2300 kg.

Description:**Assembled size:**

Basic rack: Nominal length + 60 mm

Add-on rack: Nominal length + +6 mm

Overall depth of the rack: Nominal depth + 36 mm

Application:

Ideal for industry, craft, trade, administration, archives etc. with optimum use of space.

Supplied with:

Basic rack with cross braces. One diagonal brace per extension rack.

Note:

- **Clamp feet are supplied.**
- **Floor and wall fastenings are not included.**
- **Suitable floor anchoring No. 990854.**
- **Access from one side only due to use of diagonal braces.**

- **The free unsupported length (K) must not be more than 600 mm.**
- **Supplied for self-assembly, saving freight costs. Delivered unassembled.**

Technical description

Number of shelves	7
Number of profile frames	1
Assembled size add-on rack width	1306 mm
Rack height	3000 mm
Rack installation	Extension rack
Storage shelf depth	500 mm
Rack depth	500 mm
Shelf width	1300 mm
maximum bay load	1600 kg
Shelf load capacity / maximum distributed shelf load (on metal)	150 kg
Shelf thickness	25 mm
Height adjustment interval	25 mm
Type of installation	Plug-in racking
Material	galvanized
Product name attribute	Depth 500 mm
Type of product	Storage shelf

Accessories

Shelf, galvanised width×depth 1300X500 mm	990580 1300X500
Plug-in dividers, fixed, galvanized Height × depth 300X500 mm	990581 300X500
Plug-in dividers, fixed, galvanized Height × depth 400X500 mm	990581 400X500
	990581 200X500

Plug-in dividers, fixed, galvanized Height x depth 200X500 mm

Plug-in dividers, fixed, galvanized Height x depth 500X500 mm

990581 500X500

Clamping base

990852