

**Storage shelf, basic rack, Depth 500 mm, Height / Shelf width: 3000/750mm****Order data**

|              |                 |
|--------------|-----------------|
| Order number | 990504 3000/750 |
| GTIN         | 4004514204905   |
| Item class   | 96P             |

**Description****Version:**

T-profile frames and storage shelves galvanised. Available with a maximum **bay load capacity** of 150 kg per shelf. Storage shelf levels adjustable at 25 mm intervals. Quick assembly thanks to the simple plug-in design.

**Load per bay:** for height 2000 mm 1300 kg, for 2500 mm 1700 kg, for 3000 mm 2300 kg.

**Description:****Assembled size:**

**Basic rack:** Nominal length + 60 mm

**Add-on rack:** Nominal length + +6 mm

**Overall depth of the rack:** Nominal depth + 36 mm

**Application:**

Ideal for industry, craft, trade, administration, archives etc. with optimum use of space.

**Supplied with:**

Basic rack with cross braces. One diagonal brace per extension rack.

**Note:**

- **Clamp feet are supplied.**
- **Floor and wall fastenings are not included.**
- **Suitable floor anchoring No. 990854.**
- **Access from one side only due to use of diagonal braces.**
- **The free unsupported length (K) must not be more than 600 mm.**

- **Supplied for self-assembly, saving freight costs. Delivered unassembled.**

## Technical description

|   |                 |
|---|-----------------|
| Assembled size basic rack width                                 | 810 mm          |
| Width   | 810 mm          |
| Rack installation   | Basic rack      |
| Number of profile frames  | 2               |
| Depth   | 536 mm          |
| Number of shelves   | 7               |
| Height  | 3000 mm         |
| Rack height   | 3000 mm         |
| Storage shelf depth   | 500 mm          |
| Rack depth  | 500 mm          |
| Shelf width   | 750 mm          |
| maximum bay load  | 1600 kg         |
| Shelf load capacity / maximum distributed shelf load (on metal) | 150 kg          |
| Shelf thickness   | 25 mm           |
| Height adjustment interval                                      | 25 mm           |
| Type of installation  | Plug-in racking |
| Material  | galvanized      |
| Product name attribute  | Depth 500 mm    |
| Type of product   | Storage shelf   |