



## Nut splitter, for nuts: M4-M14



### Order data

Order number	884900 M4-M14
GTIN	4021176020483
Item class	83U

### Description

#### Version:

With hydraulic ram for splitting jammed or seized nuts (grade 5 – 10) without damaging the bolts. Double curved, allowing operation even where access is difficult. With hardened chisel edge blade. Actuated by tightening the pressure screw. After the nut has been split, unscrew the nut pressure screw and push the chisel back to the stop. Size M18 – M30 for stainless steel nuts - up to M30 in strength class 8, up to M24 in strength class 10.

#### Note:

The pressure screw may be tightened to a **maximum of 60 Nm** for sizes M4 – M14 to a **maximum of 70 Nm** for sizes M14 – M24 and to a **maximum of 50 Nm** for sizes M18 – M30. Do not exceed the tightening torques; excessive torque can break the tool and cause accidents.

### Technical description

Total length without spindle screw	185 mm
Jaw capacity	7 - 24 mm
Chisel edge width	18 mm
for nuts	M4-M14
Type of product	Nut splitters

### Accessories

Spare chisel edge bit for nuts M4-M14

884910 M4-M14