

Storage shelf, basic rack, Depth 400 mm, Height / Shelf width: 2500/750mm**Order data**

Order number	990540 2500/750
GTIN	4004514237736
Item class	96P

Description**Version:**

T-profile frames and storage shelves galvanised. Available with a maximum **bay load capacity** of 250 kg per shelf. Storage shelf levels adjustable at 25 mm intervals. Quick assembly thanks to the simple plug-in design.

Load per bay: for height 2000 mm 1300 kg, for 2500 mm 1700 kg, for 3000 mm 2300 kg.

Description:**Assembled size:**

Basic rack: Nominal length + 60 mm

Extension rack: Nominal length + +6 mm

Overall depth of the rack: Nominal depth + 36 mm

Application:

Ideal for industry, craft, trade, administration, archives etc. with optimum use of space.

Supplied with:

Basic rack with cross braces. One diagonal brace per extension rack.

Note:

- **Clamp feet are supplied.**
- **Floor and wall fastenings are not included.**
- **Suitable floor anchoring No. 990854.**
- **Access from one side only due to use of diagonal braces.**
- **The free unsupported length (K) must not be more than 600 mm.**

- **Supplied for self-assembly, saving freight costs. Delivered unassembled.**

Technical description

Rack installation	Basic rack
Height	2500 mm
Assembled size basic rack width	810 mm
Number of profile frames	2
Number of shelves	6
Width	810 mm
Rack height	2500 mm
Depth	436 mm
Storage shelf depth	400 mm
Rack depth	400 mm
Shelf width	750 mm
maximum bay load	1800 kg
Shelf load capacity / maximum distributed shelf load (on metal)	250 kg
Shelf thickness	40 mm
Height adjustment interval	25 mm
Type of installation	Plug-in racking
Material	galvanized
Product name attribute	Depth 400 mm
Type of product	Storage shelf