

Storage shelf, basic rack, Depth 600 mm, Height / Shelf width: 3000/1000mm**Order data**

Order number	990508 3000/1000
GTIN	4004514202666
Item class	96P

Description**Version:**

T-profile frames and storage shelves galvanised. Available with a maximum **bay load capacity** of 150 kg per shelf. Storage shelf levels adjustable at 25 mm intervals. Quick assembly thanks to the simple plug-in design.

Load per bay: for height 2000 mm 1300 kg, for 2500 mm 1700 kg, for 3000 mm 2300 kg.

Description:**Assembled size:**

Basic rack: Nominal length + 60 mm

Add-on rack: Nominal length + +6 mm

Overall depth of the rack: Nominal depth + 36 mm

Application:

Ideal for industry, craft, trade, administration, archives etc. with optimum use of space.

Supplied with:

Basic rack with cross braces. One diagonal brace per extension rack.

Note:

- **Clamp feet are supplied.**
- **Floor and wall fastenings are not included.**
- **Suitable floor anchoring No. 990854.**
- **Access from one side only due to use of diagonal braces.**
- **The free unsupported length (K) must not be more than 600 mm.**

- **Supplied for self-assembly, saving freight costs. Delivered unassembled.**

Technical description

Rack installation	Basic rack
Number of profile frames	2
Number of shelves	7
Rack height	3000 mm
Assembled size basic rack width	1060 mm
Storage shelf depth	600 mm
Rack depth	600 mm
Shelf width	1000 mm
maximum bay load	1600 kg
Shelf load capacity / maximum distributed shelf load (on metal)	150 kg
Shelf thickness	25 mm
Height adjustment interval	25 mm
Type of installation	Plug-in racking
Material	galvanized
Product name attribute	Depth 600 mm
Type of product	Storage shelf

Accessories

Plug-in dividers, fixed, galvanized Height × depth 300X600 mm	990581 300X600
Plug-in dividers, fixed, galvanized Height × depth 500X600 mm	990581 500X600
Plug-in dividers, fixed, galvanized Height × depth 400X600 mm	990581 400X600
	990581 200X600

Plug-in dividers, fixed, galvanized Height x depth 200X600 mm

Shelf, galvanised widthxdepth 1000X600 mm

990580 1000X600

Clamping base

990852