

**Storage shelf, add-on rack, Depth 600 mm, Height / Shelf width: 2000/750mm****Order data**

|              |                 |
|--------------|-----------------|
| Order number | 990510 2000/750 |
| GTIN         | 4004514204950   |
| Item class   | 96P             |

**Description****Version:**

T-profile frames and storage shelves galvanised. Available with a maximum **bay load capacity** of 150 kg per shelf. Storage shelf levels adjustable at 25 mm intervals. Quick assembly thanks to the simple plug-in design.

**Load per bay:** for height 2000 mm 1300 kg, for 2500 mm 1700 kg, for 3000 mm 2300 kg.

**Description:****Assembled size:**

**Basic rack:** Nominal length + 60 mm

**Add-on:** Nominal length + +6 mm

**Overall depth of the rack:** Nominal depth + 36 mm

**Application:**

Ideal for industry, craft, trade, administration, archives etc. with optimum use of space.

**Supplied with:**

Basic rack with cross braces. One diagonal brace per extension rack.

**Note:**

- **Clamp feet are supplied.**
- **Floor and wall fastenings are not included.**
- **Suitable floor anchoring No. 990854.**
- **Access from one side only due to use of diagonal braces.**
- **The free unsupported length (K) must not be more than 600 mm.**

- **Supplied for self-assembly, saving freight costs. Delivered unassembled.**

## Technical description

|                                                                 |                 |
|-----------------------------------------------------------------|-----------------|
| Rack installation                                               | Extension rack  |
| Number of profile frames                                        | 1               |
| Assembled size add-on rack width                                | 756 mm          |
| Height                                                          | 2000 mm         |
| Width                                                           | 756 mm          |
| Number of shelves                                               | 5               |
| Rack height                                                     | 2000 mm         |
| Depth                                                           | 636 mm          |
| Storage shelf depth                                             | 600 mm          |
| Rack depth                                                      | 600 mm          |
| Shelf width                                                     | 750 mm          |
| maximum bay load                                                | 1300 kg         |
| Shelf load capacity / maximum distributed shelf load (on metal) | 150 kg          |
| Shelf thickness                                                 | 25 mm           |
| Height adjustment interval                                      | 25 mm           |
| Type of installation                                            | Plug-in racking |
| Material                                                        | galvanized      |
| Product name attribute                                          | Depth 600 mm    |
| Type of product                                                 | Storage shelf   |