

Storage shelf, add-on rack, Depth 400 mm, Height / Shelf width: 2000/1000mm



Order data

Order number	990542 2000/1000
GTIN	4004514202963
Item class	96P

Description

Version:

T-profile frames and storage shelves galvanised. Available with a maximum **bay load capacity** of 250 kg per shelf. Storage shelf levels adjustable at 25 mm intervals. Quick assembly thanks to the simple plug-in design.

Load per bay: for height 2000 mm 1300 kg, for 2500 mm 1700 kg, for 3000 mm 2300 kg.

Description:

Assembled size:

Basic rack: Nominal length + 60 mm

Extension rack: Nominal length + +6 mm

Overall depth of the rack: Nominal depth + 36 mm

Application:

Ideal for industry, craft, trade, administration, archives etc. with optimum use of space.

Supplied with:

Basic rack with cross braces. One diagonal brace per extension rack.

Note:

- **Clamp feet are supplied.**
- **Floor and wall fastenings are not included.**
- **Suitable floor anchoring No. 990854.**
- **Access from one side only due to use of diagonal braces.**

- **The free unsupported length (K) must not be more than 600 mm.**
- **Supplied for self-assembly, saving freight costs. Delivered unassembled.**

Technical description

Number of shelves	5
Number of profile frames	1
Assembled size add-on rack width	1006 mm
Rack installation	Extension rack
Rack height	2000 mm
Storage shelf depth	400 mm
Rack depth	400 mm
Shelf width	1000 mm
maximum bay load	1300 kg
Shelf load capacity / maximum distributed shelf load (on metal)	250 kg
Shelf thickness	40 mm
Height adjustment interval	25 mm
Type of installation	Plug-in racking
Material	galvanized
Product name attribute	Depth 400 mm
Type of product	Storage shelf

Accessories

Plug-in dividers, fixed, galvanized Height × depth 210X400 mm	990583 210X400
Shelf, galvanised width×depth 1000X400 mm	990582 1000X400
Plug-in dividers, fixed, galvanized Height × depth 510X400 mm	990583 510X400
	990583 310X400

Plug-in dividers, fixed, galvanized Height x depth 310X400 mm

Plug-in dividers, fixed, galvanized Height x depth 410X400 mm

990583 410X400

Clamping base

990852