

Ansell
Pair of gloves HyFlex® 11-920, Glove size: 8

Order data

Order number	094385 8
GTIN	10076490489400
Item class	04P

Description
Version:

HyFlex® 11-920. With Ansell Grip Technology™: Microscopically small channels in the nitrile coating draw the oil away from the contact surface and ensure a secure grip. Particularly suitable for metal production, general workshop and machine maintenance.

Standard:

EN 388; EN ISO 21420

Antistatisch gemäß EN 1149.

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

DMF-free	no
Breathability	good
Glove size	8
Heat protection	not available
Wet grip	good

Touch sensitivity	good
Oil grip	very good
silicone-free	no
Accuracy of fit	very good
Material of coating	Nitrile
Series	HyFlex®
Protection category	Category II
Type of glove	Multi-purpose gloves
Contents	12
Glove characteristics	Silicone-free
Glove characteristics	free of latex
EN 388	3131A
Backing material	Nylon
Coating	Nitrile
Coating variant	The palms of the hands
Application range	All-round
Length	246 mm
Colour	blue
Weight	25 g
Knitted technology	15G
Application	reusable
Material	Nitrile
Type of product	Multi-purpose gloves