

**Storage shelf, basic rack, Depth 400 mm, Height / Shelf width: 2500/1000mm****Order data**

Order number	990540 2500/1000
GTIN	4004514202888
Item class	96P

**Description****Version:**

T-profile frames and storage shelves galvanised. Available with a maximum **bay load capacity** of 250 kg per shelf. Storage shelf levels adjustable at 25 mm intervals. Quick assembly thanks to the simple plug-in design.

**Load per bay:** for height 2000 mm 1300 kg, for 2500 mm 1700 kg, for 3000 mm 2300 kg.

**Description:****Assembled size:**

**Basic rack:** Nominal length + 60 mm

**Extension rack:** Nominal length + +6 mm

**Overall depth of the rack:** Nominal depth + 36 mm

**Application:**

Ideal for industry, craft, trade, administration, archives etc. with optimum use of space.

**Supplied with:**

Basic rack with cross braces. One diagonal brace per extension rack.

**Note:**

- **Clamp feet are supplied.**
- **Floor and wall fastenings are not included.**
- **Suitable floor anchoring No. 990854.**
- **Access from one side only due to use of diagonal braces.**
- **The free unsupported length (K) must not be more than 600 mm.**

- **Supplied for self-assembly, saving freight costs. Delivered unassembled.**

## Technical description

Assembled size basic rack width	1060 mm
Rack installation	Basic rack
Rack height	2500 mm
Number of shelves	6
Number of profile frames	2
Storage shelf depth	400 mm
Rack depth	400 mm
Shelf width	1000 mm
maximum bay load	1800 kg
Shelf load capacity / maximum distributed shelf load (on metal)	250 kg
Shelf thickness	40 mm
Height adjustment interval	25 mm
Type of installation	Plug-in racking
Material	galvanized
Product name attribute	Depth 400 mm
Type of product	Storage shelf

## Accessories

Plug-in dividers, fixed, galvanized Height × depth 210X400 mm	990583 210X400
Plug-in dividers, fixed, galvanized Height × depth 510X400 mm	990583 510X400
Plug-in dividers, fixed, galvanized Height × depth 410X400 mm	990583 410X400
Shelf, galvanised width×depth 1000X400 mm	990582 1000X400

Plug-in dividers, fixed, galvanized Height x depth 310X400  
mm

990583 310X400

Clamping base

990852