



Pair of gloves KryTech 579, Glove size: 8



Order data

Order number	094465 8
GTIN	3245425791288
Item class	06D

Description

Version:

KryTech 579. For very delicate work in dry and less dirty working conditions. Good dexterity and very good sense of touch. **Breathable and sweat-absorbent material.**

Standard:

EN 388; EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

EN 388 abrasion resistance	4
silicone-free	yes
EN 388 penetration resistance	3
Heat protection	not available
EN 388 tear propagation resistance	4
Wet grip	medium

Material of coating	PU
Oil grip	medium
Touch sensitivity	very good
EN 388 cut resistance	3
Accuracy of fit	good
Glove size	8
DMF-free	no
Breathability	good
Type of glove	Multi-purpose gloves
Protection category	Category II
Contents	96
Glove characteristics	free of latex
EN 388	4342B
Backing material	PEHD
Coating	PU
Coating variant	The palms of the hands
Application range	Precision
Colour	grey / white
Weight	25 g
Length	220 - 270 mm
Application	reusable
Cut protection class	B
Type of product	Cut-resistant gloves