

Honeywell**Pair of gloves Polytril™ Top, Glove size: 10****Order data**

Order number	094440 10
GTIN	3603835500201
Item class	09A

Description**Version:**

Polytril™ Top. Gloves with **full nitrile coating over the wrist** for heavy-duty activities in wet and oily environments. Due to the dark colouration, very resistant to dirt. Particularly suitable for assembly work in oily and greasy environments, working outdoors under wet conditions, construction sites.

Standard:

EN 388; EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Heat protection	not available
Accuracy of fit	good
Wet grip	very good
Breathability	not available
Touch sensitivity	good

Material of coating	Nitrile
Glove size	10
DMF-free	no
Manufacturer's designation	Polytril Top
Oil grip	very good
Series	Polytril™
Protection category	Category II
Type of glove	Multi-purpose gloves
Clothing standard	Oeko-Tex Standard 100
Contents	10
Glove characteristics	Suitable for allergy sufferers
Glove characteristics	DMF-free
EN 388	4121X
Backing material	Polyamide
Coating	Nitrile
Coating variant	Full coating
Application range	Heavy Duty
Length	230 - 270 mm
Colour	black
Weight	50-70 g
Knitted technology	13G
Application	reusable
Cut protection class	1
Type of product	Multi-purpose gloves