

**Storage shelf, basic rack, Depth 800 mm, Height / Shelf width: 2000/1300mm****Order data**

Order number	990512 2000/1300
GTIN	4004514217561
Item class	96P

**Description****Version:**

T-profile frames and storage shelves galvanised. Available with a maximum **bay load capacity** of 150 kg per shelf. Storage shelf levels adjustable at 25 mm intervals. Quick assembly thanks to the simple plug-in design.

**Load per bay:** for height 2000 mm 1300 kg, for 2500 mm 1700 kg, for 3000 mm 2300 kg.

**Description:**

**Assembled size:Basic rack:** Nominal length + 60 mm**Add-on rack:** Nominal length + +6 mm**Overall depth of the rack:** Nominal depth + 36 mm

**Application:**

Ideal for industry, craft, trade, administration, archives etc. with optimum use of space.

**Supplied with:**

Basic rack with cross braces. One diagonal brace per extension rack.

**Note:**

- **Clamp feet are supplied.**
- **Floor and wall fastenings are not included.**
- **Suitable floor anchoring No. 990854.**
- **Access from one side only due to use of diagonal braces.**
- **The free unsupported length (K) must not be more than 600 mm.**
- **Supplied for self-assembly, saving freight costs. Delivered unassembled.**

## Technical description

Number of shelves	5
Rack height	2000 mm
Rack installation	Basic rack
Number of profile frames	2
Assembled size basic rack width	1360 mm
Storage shelf depth	800 mm
Rack depth	800 mm
Shelf width	1300 mm
maximum bay load	1300 kg
Shelf load capacity / maximum distributed shelf load (on metal)	150 kg
Shelf thickness	25 mm
Height adjustment interval	25 mm
Type of installation	Plug-in racking
Material	galvanized
Product name attribute	Depth 800 mm
Type of product	Storage shelf

## Accessories

Plug-in dividers, fixed, galvanized Height × depth 300X800 mm	990581 300X800
Plug-in dividers, fixed, galvanized Height × depth 500X800 mm	990581 500X800
Plug-in dividers, fixed, galvanized Height × depth 200X800 mm	990581 200X800
Shelf, galvanised width×depth 1300X800 mm	990580 1300X800
Plug-in dividers, fixed, galvanized Height × depth 400X800 mm	990581 400X800

Clamping base

990852