

Garant**Bench vice, Jaw width: 140mm****Order data**

Order number	967100 140
GTIN	4045197694171
Item class	91J

Description**Version:****Entirely of forged steel – guaranteed unbreakable.**

Slides forward on opening. With pipe clamping jaws underneath the normal jaws. Powerful, CNC-machined precision spindle with rolled thread. Spindle and guides are protected from dirt. Large hardened anvil area for shaping and upsetting work. Double adjustable guide. With solid, surface-hardened jaws (not interchangeable).

Callout:

Impact absorber washers.

Embossed measuring scale.

Guide setting: Internal hexagon screw with brass thrust washers – runs very easily.

Strong pipe jaws.

Advantage:

- **Tightening bar with impact-absorbing washers at both ends no irritating noise when the bar falls through.**
- **Long-pitch thread spindle for quick opening and closing.**
- **Interchangeable tightening bar.**
- **Opening scale embossed into slide.**

Supplied with:

Fasteners for attachment to the workbench.

Note:

For suitable height adjuster see No. 967520.

Technical description

Material	Drop forged steel
Weight	19 kg
Jaw capacity	200 mm
Clamping depth	95 mm
Opening direction	opens to the front
Pipe jaws clamp pipes with outer Ø	1 – 2.3/4 in
Jaw width	140 mm
Type of product	Machinist's vice

Accessories

Clamping system with swing jaw Jaw width 140 mm	967150 140
Bench vice mounting plate, bamboo Size 300X250	967328 300X250
Swing away mounting and height adjuster with vice Vice jaw width 140 mm	967565 140
Swivel base separate suitable for vice size 140	967140 140
Bench vice mounting plate	967330
Height adjuster for vice No. 967100 / 7110 suitable for vice size 140	967520 140