

**Bench vice LEINEN-JUNIOR, Jaw width: 150mm****Order data**

Order number	967060 150
GTIN	2050002047471
Item class	97G

**Description****Version:**

**High clamping accuracy due to Vee form precision guide.**

**Slides to the rear on opening.** High-strength casting (GG 22) with a pearlitic structure. Long and particularly accurate **Vee form precision guide.**

Precise spindle bearing; spindle fully enclosed and protected from dirt. Smooth-running spindle with trapezoidal thread (fast opening and closing of the jaws). Hardened jaws, serrated/smooth ground, reversible, and exchangeable. With large flat-milled anvil. When used with swivel base No. 967070, it can be rotated 360° and locked in any position by the clamping mechanism.

**Supplied with:**

Fasteners for attachment to the workbench.

**Colour:**

Silver-grey

**Technical description**

Jaw capacity	280 mm
Weight	40.5 kg
Opening direction	opens to the rear
Material	high-strength cast iron (GG 22)
Clamping depth	97 mm

Pipe jaws clamp pipes with outer Ø	25 - 65 mm
Jaw width	150 mm
Type of product	Machinist's vice

---

## Accessories

Bench vice mounting plate, bamboo Size 300X250	967328 300X250
Swivel base for viceLEINEN-JUNIOR Jaw width 150 mm	967070 150
Pair of spare jaws with screws, reversible serrated / smooth ground Jaw width 150 mm	967080 150
Bench vice mounting plate	967330