

Garant
Bench vice, Jaw width: 160mm

Order data

| | |
|--------------|---------------|
| Order number | 967100 160 |
| GTIN | 4045197694188 |
| Item class | 91J |

Description
Version:

Entirely of forged steel – guaranteed unbreakable.

Slides forward on opening. With pipe clamping jaws underneath the normal jaws. Powerful, CNC-machined precision spindle with rolled thread. Spindle and guides are protected from dirt. Large hardened anvil area for shaping and upsetting work. Double adjustable guide. With solid, surface-hardened jaws (not interchangeable).

Callout:

Impact absorber washers.

Embossed measuring scale.

Guide setting: Internal hexagon screw with brass thrust washers – runs very easily.

Strong pipe jaws.

Advantage:

- **Tightening bar with impact-absorbing washers at both ends no irritating noise when the bar falls through.**
- **Long-pitch thread spindle for quick opening and closing.**
- **Interchangeable tightening bar.**
- **Opening scale embossed into slide.**

Supplied with:

Fasteners for attachment to the workbench.

Note:

For suitable height adjuster see No. 967520.

Technical description

| | |
|------------------------------------|--------------------|
| Jaw capacity | 220 mm |
| Clamping depth | 110 mm |
| Opening direction | opens to the front |
| Weight | 27 kg |
| Material | Drop forged steel |
| Pipe jaws clamp pipes with outer Ø | 1 – 3.1/2 in |
| Jaw width | 160 mm |
| Type of product | Machinist's vice |

Accessories

| | |
|---|----------------|
| Bench vice mounting plate | 967330 |
| Swivel base separate suitable for vice size 160 | 967140 160 |
| Clamping system with swing jaw Jaw width 160 mm | 967150 160 |
| Height adjuster for vice No. 967100 / 7110 suitable for vice size 160 | 967520 160 |
| Bench vice mounting plate, bamboo Size 300X250 | 967328 300X250 |