



Bench vice, Jaw width: 160 mm



Order data

Order number	967100 160
GTIN	4045197694188
Item class	91J

Description

Version:

Entirely of forged steel – guaranteed unbreakable.

Slides forward on opening. With pipe clamping jaws underneath the normal jaws. Powerful, CNC-machined precision spindle with rolled thread. Spindle and guides are protected from dirt. Large hardened anvil area for shaping and upsetting work. Double adjustable guide. With solid, surface-hardened jaws (not interchangeable).

Callout:

Impact absorber washers.

Embossed measuring scale.

Guide setting: Internal hexagon screw with brass thrust washers – runs very easily.

Strong pipe jaws.

Advantage:

- **Tightening bar with impact-absorbing washers at both ends no irritating noise when the bar falls through.**
- **Long-pitch thread spindle for quick opening and closing.**
- **Interchangeable tightening bar.**
- **Opening scale embossed into slide.**

Supplied with:

Fasteners for attachment to the workbench.

Note:

For suitable height adjuster see No. 967520.

Jaw capacity: 220 mm

Clamping depth: 110 mm

Pipe jaws clamp pipes with outer Ø: 1 – 3.1/2 inch
 Weight: 27 kg

Technical description

Jaw capacity	220 mm
Clamping depth	110 mm
Opening direction	opens to the front
Weight	27 kg
Material	Drop forged steel
Pipe jaws clamp pipes with outer Ø	1 – 3.1/2 inch
Jaw width	160 mm
Type of product	Machinist's vice

Accessories

Swivel base separate suitable for vice size 160	967140 160
Clamping system with swing jaw Jaw width 160 mm	967150 160
Height adjuster for vice No. 967100 / 7110 suitable for vice size 160	967520 160
Bench vice mounting plate	967330
Bench vice mounting plate, bamboo Size 300X250	967328 300X250