

**Garant****Bench vice with swivel base, Jaw width: 80mm****Order data**

|              |               |
|--------------|---------------|
| Order number | 967010 80     |
| GTIN         | 4045197612236 |
| Item class   | 91J           |

**Description****Version:****High clamping accuracy due to Vee form precision guide.**

**Slides to the rear on opening.** High-strength casting (GG 25) with a pearlitic structure. Long and particularly accurate **Vee form precision guide**. Precise spindle bearing, lead spindle is fully enclosed with trapezoidal thread and hence protected from dirt. Large flat milled anvil area for light shaping work. The hardened steel jaws are grooved and can be exchanged for ground jaws (see spare jaws).

**With swivel base** for 360° rotation can be locked in any position by the clamping mechanism.

**Supplied with:**

Fasteners for attachment to the workbench.

**Colour:**

Silver-grey.

**Technical description**

|                   |                                 |
|-------------------|---------------------------------|
| Jaw capacity      | 100 mm                          |
| Material          | high-strength cast iron (GG 25) |
| Opening direction | opens to the rear               |
| Jaw width         | 80 mm                           |

Type of product

Machinist's vice

---

**Accessories**

|  |                |
|--|----------------|
| Bench vice mounting plate                        | 967330         |
| Pair of spare jaws serrated Jaw width 80 mm      | 967040 80      |
| Swivel base separate Jaw width 80 mm             | 967020 80      |
| Pair of spare jaws smooth ground Jaw width 80 mm | 967045 80      |
| Bench vice mounting plate, bamboo Size 300X250   | 967328 300X250 |