

Garant**Bench vice with swivel base, Jaw width: 100mm****Order data**

Order number	967010 100
GTIN	4045197612243
Item class	91J

Description**Version:****High clamping accuracy due to Vee form precision guide.**

Slides to the rear on opening. High-strength casting (GG 25) with a pearlitic structure. Long and particularly accurate **Vee form precision guide**. Precise spindle bearing, lead spindle is fully enclosed with trapezoidal thread and hence protected from dirt. Large flat milled anvil area for light shaping work. The hardened steel jaws are grooved and can be exchanged for ground jaws (see spare jaws).

With swivel base for 360° rotation can be locked in any position by the clamping mechanism.

Supplied with:

Fasteners for attachment to the workbench.

Colour:

Silver-grey.

Technical description

Jaw capacity	145 mm
Opening direction	opens to the rear
Material	high-strength cast iron (GG 25)
Weight	21 kg

Jaw width	100 mm
Type of product	Machinist's vice

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/967010-100>