

**Garant****Bench vice with swivel base, Jaw width: 100mm****Order data**

Order number	967010 100
GTIN	4045197612243
Item class	91J

**Description****Version:****High clamping accuracy due to Vee form precision guide.**

**Slides to the rear on opening.** High-strength casting (GG 25) with a pearlitic structure. Long and particularly accurate **Vee form precision guide**. Precise spindle bearing, lead spindle is fully enclosed with trapezoidal thread and hence protected from dirt. Large flat milled anvil area for light shaping work. The hardened steel jaws are grooved and can be exchanged for ground jaws (see spare jaws).

**With swivel base** for 360° rotation can be locked in any position by the clamping mechanism.

**Supplied with:**

Fasteners for attachment to the workbench.

**Colour:**

Silver-grey.

**Technical description**

Jaw capacity	145 mm
Opening direction	opens to the rear
Material	high-strength cast iron (GG 25)
Jaw width	100 mm

Type of product	Machinist's vice
-----------------	------------------

## Accessories

Pair of magnetic vice jawsAluminium, smooth, standard Jaw width 100 mm	967721 100
Bench vice mounting plate, bamboo Size 300X250	967328 300X250
Pair of magnetic vice jawsAluminium / fibre cover, smooth Jaw width 100 mm	967724 100
Pair of magnetic vice jawspolyurethane, Vee form Jaw width 100 mm	967729 100
Pair of light metal vice jaws with spring clips Jaw width 100 mm	967711 100
Pair of spare jaws serrated Jaw width 100 mm	967040 100
Bench vice mounting plate	967330
Swivel base separate Jaw width 100 mm	967020 100
Pair of magnetic vice jawsFelt, smooth Jaw width 100 mm	967726 100
Pair of magnetic vice jawsAluminium, profiled Jaw width 100 mm	967722 100
Pair of spare jaws smooth ground Jaw width 100 mm	967045 100
Pair of magnetic vice jawsAluminium, Vee form Jaw width 100 mm	967723 100
Pair of magnetic vice jawsRubber, smooth Jaw width 100 mm	967727 100
Pair of magnetic vice jawspolyurethane, serrated Jaw width 100 mm	967728 100