



Table / bench vice with bench clamp, Jaw width: 60 mm



Order data

Order number	967030 60
GTIN	4045197612311
Item class	91J

Description

Version:

High clamping accuracy due to Vee form precision guide.

Slides to the rear on opening. High-strength casting (GG 25) with a pearlitic structure. Long and particularly accurate **Vee form precision guide**. Precise spindle bearing, lead spindle is fully enclosed with trapezoidal thread and hence protected from dirt. Large face milled anvil area for light shaping work. The hardened steel jaws are ground and can be exchanged for serrated jaws (see spare jaws).

Application:

For clamping to the worktop.

Jaw capacity: 65 mm

Weight: 2.5 kg

Technical description

Jaw capacity	65 mm
Weight	2.5 kg
Material	high-strength cast iron (GG 25)

Opening direction	opens to the rear
Jaw width	60 mm
Type of product	Machinist's vice

Accessories

Pair of spare jaws smooth ground Jaw width 60 mm	967045 60
Bench vice mounting plate	967330
Bench vice mounting plate, bamboo Size 300X250	967328 300X250