

Garant**Bench vice with swivel base, Jaw width: 125mm****Order data**

Order number	967010 125
GTIN	4045197612250
Item class	91J

Description**Version:****High clamping accuracy due to Vee form precision guide.**

Slides to the rear on opening. High-strength casting (GG 25) with a pearlitic structure. Long and particularly accurate **Vee form precision guide**. Precise spindle bearing, lead spindle is fully enclosed with trapezoidal thread and hence protected from dirt. Large flat milled anvil area for light shaping work. The hardened steel jaws are grooved and can be exchanged for ground jaws (see spare jaws).

With swivel base for 360° rotation can be locked in any position by the clamping mechanism.

Supplied with:

Fasteners for attachment to the workbench.

Colour:

Silver-grey.

Technical description

Weight	37 kg
Jaw capacity	190 mm
Opening direction	opens to the rear
Material	high-strength cast iron (GG 25)

Jaw width	125 mm
Type of product	Machinist's vice

Accessories

Swivel base separate Jaw width 125 mm	967020 125
Pair of spare jaws serrated Jaw width 125 mm	967040 125
Pair of spare jaws smooth ground Jaw width 125 mm	967045 125
Bench vice mounting plate, bamboo Size 300X250	967328 300X250
Bench vice mounting plate	967330
Magnetic vice jaw set Jaw width 125 mm	967702 125
Pair of light metal vice jaws with spring clips Jaw width 125 mm	967711 125
Pair of magnetic vice jaws Aluminium, smooth, standard Jaw width 125 mm	967721 125
Pair of magnetic vice jaws Aluminium, profiled Jaw width 125 mm	967722 125
Pair of magnetic vice jaws Aluminium, Vee form Jaw width 125 mm	967723 125
Pair of magnetic vice jaws Aluminium / fibre cover, smooth Jaw width 125 mm	967724 125
Pair of magnetic vice jaws Felt, smooth Jaw width 125 mm	967726 125
Pair of magnetic vice jaws Rubber, smooth Jaw width 125 mm	967727 125
Pair of magnetic vice jaws polyurethane, serrated Jaw width 125 mm	967728 125
Pair of magnetic vice jaws polyurethane, Vee form Jaw width 125 mm	967729 125