

Garant**Bench vice with swivel base, Jaw width: 100mm****Order data**

Order number	967120 100
GTIN	4045197612557
Item class	91J

Description**Version:**

Entirely of forged steel – guaranteed unbreakable.

Slides forward on opening. With pipe clamping jaws underneath the normal jaws. Powerful, CNC-machined precision spindle with rolled thread. Spindle and guides are protected from dirt. Large hardened anvil area for shaping and upsetting work. Double adjustable guide. With solid, surface-hardened jaws (not interchangeable).

Advantage:

- **Tightening bar with impact-absorbing washers at both ends no irritating noise when the bar falls through.**
- **Long-pitch thread spindle for quick opening and closing.**
- **Interchangeable tightening bar.**
- **Opening scale embossed into slide.**

Supplied with:

Fasteners for attachment to the workbench.

Note:

For suitable height adjuster see No. 967520.

Technical description

Material	Drop forged steel
Opening direction	opens to the front

Jaw width	100 mm
exchangeable jaws	no
Type of product	Machinist's vice

Accessories

Pair of magnetic vice jaws polyurethane, serrated Jaw width 100 mm	967728 100
Bench vice mounting plate, bamboo Size 300X250	967328 300X250
Pair of magnetic vice jaws polyurethane, Vee form Jaw width 100 mm	967729 100
Pair of magnetic vice jaws Rubber, smooth Jaw width 100 mm	967727 100
Pair of magnetic vice jaws Aluminium / fibre cover, smooth Jaw width 100 mm	967724 100
Pair of magnetic vice jaws Aluminium, profiled Jaw width 100 mm	967722 100
Pair of magnetic vice jaws Aluminium, smooth, standard Jaw width 100 mm	967721 100
Pair of magnetic vice jaws Felt, smooth Jaw width 100 mm	967726 100
Bench vice mounting plate	967330
Swivel base separate suitable for vice size 100	967140 100
Pair of light metal vice jaws with spring clips Jaw width 100 mm	967711 100
Pair of magnetic vice jaws Aluminium, Vee form Jaw width 100 mm	967723 100