

## Bench vice LEINEN-JUNIOR, Jaw width: 100mm



### Order data

Order number	967060 100
GTIN	2050002047457
Item class	97G

### Description

#### Version:

#### High clamping accuracy due to Vee form precision guide.

**Slides to the rear on opening.** High-strength casting (GG 22) with a pearlitic structure. Long and particularly accurate **Vee form precision guide.**

Precise spindle bearing; spindle fully enclosed and protected from dirt. Smooth-running spindle with trapezoidal thread (fast opening and closing of the jaws). Hardened jaws, serrated/smooth ground, reversible, and exchangeable. With large flat-milled anvil. When used with swivel base No. 967070, it can be rotated 360° and locked in any position by the clamping mechanism.

#### Supplied with:

Fasteners for attachment to the workbench.

#### Colour:

Silver-grey

### Technical description

Opening direction	opens to the rear
Weight	12 kg
Material	high-strength cast iron (GG 22)
Jaw capacity	140 mm
Clamping depth	84 mm

Pipe jaws clamp pipes with outer Ø	16 - 75 mm
Jaw width	100 mm
Type of product	Machinist's vice

## Accessories

Height adjuster for LEINEN JUNIOR bench vice No. 967060 suitable for vice size 100	967510 100
Pair of magnetic vice jaws Aluminium / fibre cover, smooth Jaw width 100 mm	967724 100
Pair of magnetic vice jaws polyurethane, serrated Jaw width 100 mm	967728 100
Pair of magnetic vice jaws Rubber, smooth Jaw width 100 mm	967727 100
Pair of magnetic vice jaws Aluminium, Vee form Jaw width 100 mm	967723 100
Pair of magnetic vice jaws Aluminium, profiled Jaw width 100 mm	967722 100
Pair of magnetic vice jaws Aluminium, smooth, standard Jaw width 100 mm	967721 100
Swivel base for vice LEINEN-JUNIOR Jaw width 100 mm	967070 100
Pair of magnetic vice jaws Felt, smooth Jaw width 100 mm	967726 100
Pair of magnetic vice jaws polyurethane, Vee form Jaw width 100 mm	967729 100
Pair of spare jaws with screws, reversible serrated / smooth ground Jaw width 100 mm	967080 100
Pair of light metal vice jaws with spring clips Jaw width 100 mm	967711 100
Bench vice mounting plate, bamboo Size 300X250	967328 300X250
Bench vice mounting plate	967330