

**Garant****Bench vice with swivel base, Jaw width: 120mm****Order data**

Order number	967120 120
GTIN	4045197612564
Item class	91J

**Description****Version:**

**Entirely of forged steel – guaranteed unbreakable.**

**Slides forward on opening.** With pipe clamping jaws underneath the normal jaws. Powerful, CNC-machined precision spindle with rolled thread. Spindle and guides are protected from dirt. Large hardened anvil area for shaping and upsetting work. Double adjustable guide. With solid, surface-hardened jaws (not interchangeable).

**Advantage:**

- **Tightening bar with impact-absorbing washers at both ends no irritating noise when the bar falls through.**
- **Long-pitch thread spindle for quick opening and closing.**
- **Interchangeable tightening bar.**
- **Opening scale embossed into slide.**

**Supplied with:**

Fasteners for attachment to the workbench.

**Note:**

For suitable height adjuster see No. 967520.

**Technical description**

Material	Drop forged steel
Opening direction	opens to the front

Jaw width	120 mm
exchangeable jaws	no
Type of product	Machinist's vice

---

## Accessories

Clamping system with swing jaw Jaw width 120 mm	967150 120
Swivel base separate suitable for vice size 120	967140 120
Bench vice mounting plate, bamboo Size 300X250	967328 300X250
Bench vice mounting plate	967330