

**Garant****Bench vice, Jaw width: 100mm****Order data**

Order number	967100 100
GTIN	4045197694157
Item class	91J

**Description****Version:****Entirely of forged steel – guaranteed unbreakable.**

**Slides forward on opening.** With pipe clamping jaws underneath the normal jaws. Powerful, CNC-machined precision spindle with rolled thread. Spindle and guides are protected from dirt. Large hardened anvil area for shaping and upsetting work. Double adjustable guide. With solid, surface-hardened jaws (not interchangeable).

**Callout:**

Impact absorber washers.

Embossed measuring scale.

Guide setting: Internal hexagon screw with brass thrust washers – runs very easily.

Strong pipe jaws.

**Advantage:**

- **Tightening bar with impact-absorbing washers at both ends no irritating noise when the bar falls through.**
- **Long-pitch thread spindle for quick opening and closing.**
- **Interchangeable tightening bar.**
- **Opening scale embossed into slide.**

**Supplied with:**

Fasteners for attachment to the workbench.

**Note:**

For suitable height adjuster see No. 967520.

**Technical description**

Clamping depth	65 mm
Opening direction	opens to the front
Weight	6 kg
Material	Drop forged steel
Jaw capacity	90 mm
Pipe jaws clamp pipes with outer Ø	3/4 – 1.3/4 in
Jaw width	100 mm
Type of product	Machinist's vice

## Accessories

Height adjuster for vice No. 967100 / 7110 suitable for vice size 100	967520 100
Pair of magnetic vice jaws polyurethane, serrated Jaw width 100 mm	967728 100
Pair of magnetic vice jaws Aluminium, smooth, standard Jaw width 100 mm	967721 100
Swing away mounting and height adjuster with vice Vice jaw width 100 mm	967565 100
Pair of magnetic vice jaws Aluminium, profiled Jaw width 100 mm	967722 100
Bench vice mounting plate	967330
Pair of magnetic vice jaws polyurethane, Vee form Jaw width 100 mm	967729 100
Pair of magnetic vice jaws Aluminium, Vee form Jaw width 100 mm	967723 100
Swivel base separate suitable for vice size 100	967140 100
Bench vice mounting plate, bamboo Size 300X250	967328 300X250
Pair of light metal vice jaws with spring clips Jaw width 100 mm	967711 100
	967727 100

Pair of magnetic vice jawsRubber, smooth Jaw width 100 mm

Pair of magnetic vice jawsFelt, smooth Jaw width 100 mm

967726 100

Pair of magnetic vice jawsAluminium / fibre cover, smooth  
Jaw width 100 mm

967724 100