

**Bench vice LEINEN-JUNIOR, Jaw width: 125mm****Order data**

Order number	967060 125
GTIN	2050002047464
Item class	97G

**Description****Version:**

**High clamping accuracy due to Vee form precision guide.**

**Slides to the rear on opening.** High-strength casting (GG 22) with a pearlitic structure. Long and particularly accurate **Vee form precision guide.**

Precise spindle bearing; spindle fully enclosed and protected from dirt. Smooth-running spindle with trapezoidal thread (fast opening and closing of the jaws). Hardened jaws, serrated/smooth ground, reversible, and exchangeable. With large flat-milled anvil. When used with swivel base No. 967070, it can be rotated 360° and locked in any position by the clamping mechanism.

**Supplied with:**

Fasteners for attachment to the workbench.

**Colour:**

Silver-grey

**Technical description**

Clamping depth	88 mm
Material	high-strength cast iron (GG 22)
Opening direction	opens to the rear
Weight	24 kg
Jaw capacity	180 mm

Pipe jaws clamp pipes with outer Ø	16 - 68 mm
Jaw width	125 mm
Type of product	Machinist's vice

## Accessories

Bench vice mounting plate, bamboo Size 300X250	967328 300X250
Pair of magnetic vice jawsAluminium, smooth, standard Jaw width 125 mm	967721 125
Height adjuster for LEINEN JUNIOR bench vice No. 967060 suitable for vice size 125	967510 125
Swivel base for viceLEINEN-JUNIOR Jaw width 125 mm	967070 125
Pair of magnetic vice jawspolyurethane, Vee form Jaw width 125 mm	967729 125
Pair of magnetic vice jawsAluminium / fibre cover, smooth Jaw width 125 mm	967724 125
Pair of light metal vice jaws with spring clips Jaw width 125 mm	967711 125
Pair of magnetic vice jawsAluminium, profiled Jaw width 125 mm	967722 125
Pair of magnetic vice jawsRubber, smooth Jaw width 125 mm	967727 125
Pair of magnetic vice jawsFelt, smooth Jaw width 125 mm	967726 125
Pair of magnetic vice jawsAluminium, Vee form Jaw width 125 mm	967723 125
Pair of magnetic vice jawspolyurethane, serrated Jaw width 125 mm	967728 125
Pair of spare jaws with screws, reversible serrated / smooth ground Jaw width 125 mm	967080 125
Bench vice mounting plate	967330
Magnetic vice jaw set Jaw width 125 mm	967702 125