

Garant
Bench vice, Jaw width: 120 mm

Order data

Order number	967100 120
GTIN	4045197694164
Item class	91J

Description
Version:

Entirely of forged steel – guaranteed unbreakable.

Slides forward on opening. With pipe clamping jaws underneath the normal jaws. Powerful, CNC-machined precision spindle with rolled thread. Spindle and guides are protected from dirt. Large hardened anvil area for shaping and upsetting work. Double adjustable guide. With solid, surface-hardened jaws (not interchangeable).

Callout:

Impact absorber washers.

Embossed measuring scale.

Guide setting: Internal hexagon screw with brass thrust washers – runs very easily.

Strong pipe jaws.

Advantage:

- **Tightening bar with impact-absorbing washers at both ends no irritating noise when the bar falls through.**
- **Long-pitch thread spindle for quick opening and closing.**
- **Interchangeable tightening bar.**
- **Opening scale embossed into slide.**

Supplied with:

Fasteners for attachment to the workbench.

Note:

For suitable height adjuster see No. 967520.

Jaw capacity: 150 mm

Clamping depth: 80 mm

Pipe jaws clamp pipes with outer Ø: 1 – 2.1/2 inch

Weight: 11 kg

Technical description

Weight	11 kg
Clamping depth	80 mm
Opening direction	opens to the front
Material	Drop forged steel
Jaw capacity	150 mm
Pipe jaws clamp pipes with outer Ø	1 – 2.1/2 inch
Jaw width	120 mm
Type of product	Machinist's vice

Accessories

Swivel base separate suitable for vice size 120	967140 120
Clamping system with swing jaw Jaw width 120 mm	967150 120
Height adjuster for vice No. 967100 / 7110 suitable for vice size 120	967520 120
Swing away mounting and height adjuster with vice Vice jaw width 120 mm	967565 120
Bench vice mounting plate	967330
Bench vice mounting plate, bamboo Size 300X250	967328 300X250