


Garant

Heavy-duty basic rack with 2 column stiles, Usable depth 1350 mm, Height: 2500mm

**Order data**

Order number	993000 2500
GTIN	4045197521859
Item class	91W

Description**Version:**

Frame stiles of C-profile 100 mm wide. With insertion holes every 50 mm for insertion of pull-out shelves. With locking bar (anti-tip protection), top shelf and rear panel (4 pieces for size 2000, 5 pieces for size 2500).

Application:

For fitting in conjunction with pull-out shelves No. 993101; 993111, together with side panels No. 993260; 993270, and swing doors No. 993321; 993331, and electrically-operated roller shutter No. 993310 – 993316.

Colour:

Light grey RAL 7035 **powder-coated.**

Note:

- **For safety the rack base plates must be anchored to the floor with suitable fastenings.**
- **Supplied for self-assembly, saving freight costs. Delivered unassembled.**

Technical description

Bay load (individual bay)	4000 kg
---------------------------	---------

Usable height	2390 mm
maximum fitting with pull-out shelves/storage shelves	4
Height	2500 mm
Top shelf	500 kg
Material thickness	2 mm
Cabinet housing internal load capacity	4000 kg
Drawer runner extension	Anti-tilt lock
Height adjustment interval	50 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	Usable depth 1350 mm
Width	1120 mm
Depth	1370 mm
Usable width	920 mm
Usable depth	1350 mm
Placing a pallet into storage	Pallets lengthways insertion
Type of product	Heavy-duty racking