



Pair of gloves KryTech 579, Glove size: 10



Order data

Order number	094465 10
GTIN	3245425791202
Item class	06D

Description

Version:

KryTech 579. For very delicate work in dry and less dirty working conditions. Good dexterity and very good sense of touch. **Breathable and sweat-absorbent material.**

Standard:

EN 388; EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Accuracy of fit	good
EN 388 abrasion resistance	4
Wet grip	medium
Touch sensitivity	very good
Material of coating	PU
EN 388 cut resistance	3

Glove size	10
Heat protection	not available
DMF-free	no
Breathability	good
EN 388 penetration resistance	3
silicone-free	yes
EN 388 tear propagation resistance	4
Oil grip	medium
Protection category	Category II
Type of glove	Multi-purpose gloves
Contents	96
Glove characteristics	free of latex
EN 388	4342B
Backing material	PEHD
Coating	PU
Coating variant	The palms of the hands
Application range	Precision
Colour	grey / white
Weight	25 g
Length	220 - 270 mm
Application	reusable
Cut protection class	B
Type of product	Cut-resistant gloves